

# Instrumentation Accessories

## 580007 (46785-00)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
11/2024

## Table of Contents

General Description _____	3
Specifications _____	3

## General Description

The Instrumentation Accessories set contains the accessories required for pressure measurements. The set includes nipples with pressure measurement port, and plastic tubing.

## Specifications

Parameter	Value
<b>Nipple 12.7 mm (1/2 in), with pressure measurement port</b>	
Quantity	4
Length	10.2 cm (4 in)
<b>Tube Cutter</b>	For tubing 6.35-12.7 mm (1/4-1/2 in)
<b>Tubing</b>	
Type	Polyethylene, 6.35 mm (1/4 in) O.D., 4.5 m (180 in) long
Maximum Operating Pressure	700 kPa (100 psi)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**