

# Signal Tower

## 582351 (5924-00)

**FESTO**

**LabVolt Series**

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
02/2025

Table of Contents

General Description \_\_\_\_\_ 3

Specifications \_\_\_\_\_ 3

## General Description

The Signal Tower consists of three lights providing visual signals of the FMS states. Lights are stacked one upon another. Each module is easily programmable without any special wiring or tools. An Acoustic Alarm, Model 52054, is available as an option.

## Specifications

Parameter	Value
Lights	3 (green, red, and yellow)
Inputs (6)	24 V dc
Physical Characteristics	
Dimensions (H x W x D)	368 x 170 x 170 mm (14.5 x 6.7 x 6.7 in)
Net Weight	1.3 kg (2.8 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**