

**Pressure Gauge: Analog – Low Range – 0-100 kPa
(0-15 psig)
582374 (6553-00)**

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description	3
Specifications	3

General Description

The Pressure Gauge provides a direct reading of the pressure in one of many convenient measurement units. It features two interconnected pressure ports, and is equipped with a mounting bracket for simple installation on the workstation.

Specifications

Parameter	Value
Pressure Gauge	
Type	Analog, bourdon tube
Range	0-100 kPa (0-15 psig)
Accuracy	±3% of full scale
Dial Diameter	6.4 cm (2.5 in)
Pressure Taps	Two inlets with quick-connect ball-check socket
Physical Characteristics	
Dimensions (H x W x D)	11.43 x 12 x 10.48 cm (4.5 x 4.7 x 4.125 in)
Net Weight	0.5 kg (1.1 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com