

HART/FOUNDATION Fieldbus Software Configurator 588422 (46982-B0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
04/2025

Table of Contents

General Description	3
List of Manuals	3
Table of Contents of the Manual(s)	3
Specifications	3

General Description

The Software Configurator includes the FieldCare software necessary to interpret the data related to the different smart devices and to configure their parameters. The HART version also includes a communication box for data transfer between a HART device and a PC with a USB port. The FOUNDATION Fieldbus version makes use of the FOUNDATION Fieldbus Bridge instead, Model 46979-1.

Available versions:

- 46982-0 HART Software Configurator
- 46982-A FOUNDATION Fieldbus Software Configurator
- 46982-B HART/FOUNDATION Fieldbus Software Configurator

List of Manuals

Description	Manual number
HART Device Configuration (Workbook)	585164 (86050-00)
HART Device Configuration (Workbook (Instructor))	585165 (86050-10)
FOUNDATION™ Fieldbus Networking (User Guide)	585312 (89454-E0)

Table of Contents of the Manual(s)

HART Device Configuration (Workbook) (585164 (86050-00))

- 2-1 Two-Wire Transmitter
- 2-2 Four-Wire Transmitter (Optional)
- 2-3 Output Device (Optional)
- 3-1 HART Multidrop with Multiple Transmitters

Specifications

Parameter	Value
Computer Requirements	A currently available personal computer running under one of the following operating systems: Windows® 7 or Windows® 8.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com