

# 3AC Power Supply and Safety Unit 594826 (8825-PC)

# FESTO

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en 230 V - 50 Hz  
10/2021

## Table of Contents

General Description	2
Specifications	2

### General Description

The 3AC Power Supply and Safety Unit consists of a fixed-voltage three-phase ac power source enclosed in a module. The 3AC Power Supply and Safety Unit comprises single-phase and three-phase ac power outlets with overcurrent protection and type B residual current protection. It also includes the following features for additional safety: lockable power-on switch, emergency stop button, undervoltage release, and single-phase, earthed and polarized ac power outlets. It can be used to power the 3AC 400V/DC 230V/Power Supply using the color-coded safety banana jacks.

Indicator lamps indicate the presence of output voltage on each phase.

### Specifications

Parameter	Value
<b>Module Requirements</b>	
Maximum Current	10 A
AC Power Network Installation	3 phases (230/400 V – 50 Hz), star (wye) configuration including neutral and ground wires, protected by a circuit breaker of 20 A.
<b>Residual Current Device</b>	
Type	B
Current	30 mA
<b>Outputs</b>	
Fixed-Voltage, Three-Phase AC Power Source	230/400 V – 10 A
Fixed-Voltage, Single-Phase AC Power Source (3)	230 V – 10 A
<b>Conformity/Directives</b>	CE and RoHS
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	297 x 266 x 140 mm
Net Weight	4,6 kg

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2021. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

[www.labvolt.com](http://www.labvolt.com)

[www.festo-didactic.com](http://www.festo-didactic.com)