

Multimeters Module

586888 (8946-A0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
05/2025

Table of Contents

General Description	3
Specifications	3

General Description

The Multimeters Module consists of three Digital Multimeters installed on the front panel of a half-size module. This allows the Multimeters Module to be inserted in an EMS Workstation, just like any other module.

Specifications

Parameter	Value
Multimeters	
Quantity	3
Voltage Range	0-600 V dc and ac
Current Range	0-10 A dc
Resistance Range	0-20 M Ω
Physical Characteristics	
Dimensions (H x W x D)	154 x 287 x 440 mm (6.1 x 11.3 x 17.3 in)
Net Weight	TBE

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com