


Pressure Gauge – 210 kPa (30 psi) 579992 (46761-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description	3
Specifications	3

General Description

The Pressure Gauge provides a direct visual reading of the measured pressure. The Pressure Gauge is fixed to a mounting bracket to be attached to metal struts. It has a maximum operating pressure of 210 kPa (30 psi). A version with a maximum operating range of 700 kPa (100 psi) is also available: Model 46761-A.

Specifications

Parameter	Value
Maximum Operating Pressure	210 kPa (30 psi)
Units	kPa, psi
Physical Characteristics	
Dimensions (H x W x D)	140 x 140 x 60 mm (5.5 x 5.5 x 2.3 in)
Net Weight	0.73 kg (1.6 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com