


FACET Breadboard

581221 (91091-20)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description _____	3
Topic Coverage _____	3
Features & Benefits _____	3
List of Manuals _____	3
Table of Contents of the Manual(s) _____	3

General Description

The Breadboard module is a good complement to Digital Logic Fundamentals (Model 91014) but it can also be used for teachers' custom exercises or student projects. The Breadboard module consists of three printed circuit boards designed so that students can easily connect and change circuits without the need to sold components. Students gain the understanding of the physical characteristics of components like pinouts, size, power, and impedance voltage limits. The breadboard comes with all the leads and components required to connect the studied circuits. These circuits include astable, bistable, and monostable multivibrators, as well as Schmitt trigger (wave-squaring) circuits. A voltage source powered from the base unit provides the voltages required to power the circuits. These voltages are accessible from an additional solderless breadboard. The practical, hands-on approach of the courseware guides students in the observation and measurement of signals with an oscilloscope. As a prerequisite, students should be familiar with the operation of bipolar transistor circuits.

Topic Coverage

- Astable Multivibrator
- Bistable Multivibrator
- Monostable Multivibrator
- Schmitt Trigger

Features & Benefits

- Three printed circuit boards designed so that students can easily connect and change circuits without the need to solder components.
- All the leads and components required to connect the studied circuits.
- Astable, bistable, and monostable multivibrators
- Schmitt trigger (wave-squaring) circuits

List of Manuals

Description	Manual number
Basics of Multivibrator Circuits (Workbook) _____	580399 (37967-00)
Basics of Multivibrator Circuits (Workbook (Instructor)) _____	580400 (37967-10)

Table of Contents of the Manual(s)

Basics of Multivibrator Circuits (Workbook) (580399 (37967-00))

- 1 Astable Multivibrator
- 2 Bistable Multivibrator
- 3 Monostable Multivibrator
- 4 Schmitt Trigger

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com