

# Industrial Controls Mobile Workstation 581240 (3103-40)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
11/2024

## Table of Contents

General Description _____	3
Manual _____	3
Specifications _____	3

## General Description

The Industrial Controls Mobile Workstation is a double-sided, mobile workstation on casters. The workstation has an A-frame configuration, is constructed of steel, and can accommodate two student groups simultaneously. Four pairs of mounting rails hold the control modules firmly in place. Additional mounting rails underneath the work surface increase the workstation storage capability. The work surface and storage shelf are protected against scratches by a rubber carpet.

Safety bars are attached to each rail of the Industrial Controls Mobile Workstation. These bars prevent students from removing modules during laboratory exercises. Padlocks are provided to lock the safety bars in place once all modules are inserted in the workstation.

## Manual

### Description

### Manual number

Industrial Controls Training Systems Series 3100 (User Guide) \_\_\_\_\_ 583973 (27073-E0)

## Specifications

Parameter	Value
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	1930 x 1168 x 711 mm (76 x 46 x 28 in)
Net Weight	109 kg (240 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**