


Ni-MH Battery Charger Function Set

581439 (8968-50)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description	3
Specifications	4

General Description

The Ni-MH Battery Charger Function Set is a package of control functions that can be activated in the Four-Quadrant Dynamometer/Power Supply, enabling the module to operate as different types of Ni-MH battery chargers, as well as a battery discharger.

The control functions in the set are only available in computer-based mode. This means that the function performed by the Four-Quadrant Dynamometer/Power Supply is selected, set, and monitored using the LVDAC-EMS software. The following control functions are available in the set:

Power Supply operating mode

- Ni-MH Battery Charger (Constant-Current Charge with Voltage Cutoff and TCO): this function implements a basic Ni-MH battery charger. This charger forces a constant charge in the battery until the battery voltage reaches a certain value at which the charge terminates. The charger also monitors the battery temperature during charge. Battery charging is terminated immediately when the battery temperature reaches a specific cutoff temperature. The user has control over the charge current, cutoff voltage, and cutoff temperature.
- Ni-MH Battery Charger (Constant-Current Timed Charge with TCO): this function implements a time-controlled Ni-MH battery charger. This charger forces a constant charge current in the battery during a specific period of time and then turns off. The charger also monitors the battery temperature during charge. Battery charging is terminated immediately when the battery temperature reaches a specific cutoff temperature. The user has control over the charge current, charge duration, and cutoff temperature.
- Ni-MH Battery Charger (Constant-Current Charge with -dV and TCO): this function implements an advanced Ni-MH battery charger. This charger forces a constant charge current in the battery until the battery voltage, which increases steadily from the beginning of charge, reaches a plateau and decreases by a certain amount (-dV), at which point the charge terminates. The charger also monitors the battery temperature during charge. Battery charging is terminated immediately when the battery temperature reaches a specific cutoff temperature. The user has control over the charge current, voltage drop (-dV), and cutoff temperature.
- Ni-MH Battery Charger (Constant-Current Charge with dT°/dt and TCO): this function implements an advanced Ni-MH battery charger. This charger monitors the battery temperature and forces a constant charge current in the battery until the rate of increase of the battery temperature (dT°/dt) reaches a specific value, at which point the charge terminates. Battery charging can also terminate when the battery temperature reaches a specific cutoff temperature. The user has control over the charge current, maximum rate of temperature increase (dT°/dt), and cutoff temperature.
- Ni-MH Battery Charger (Three-Step Charge with TCO): this function implements a fast Ni-MH battery charger (three-step charge algorithm). Battery charging begins by forcing a constant charge current in the battery until the rate of increase of the battery temperature (dT°/dt) reaches a specific value. At this point, the charger enters the second phase of the charge process and continues battery charging with a constant current having a lower value for a specific period. After this period, battery charging continues with a constant current of very low value. The charger monitors the battery temperature during charge. Battery charging can also terminate when the battery temperature reaches a specific cutoff temperature. The user has control over the charge current for each of the three phases of the charging process, maximum rate of temperature increase (dT°/dt) used during the first phase of charge, duration of the second phase of charge, and cutoff temperature.
- Battery Discharger (Constant-Current Timed Discharge with Voltage Cutoff): this function sinks a constant current from a battery, thereby discharging the battery at a specific rate, during a specific period. The discharger also monitors the battery voltage during discharge. Battery discharging terminates immediately when the battery voltage decreases to a specific cutoff voltage. The user has control over the discharge current, discharge duration, and cutoff voltage.

Specifications

Parameter	Value
Control Functions	
Control Functions	Ni-MH Battery Charger (Constant-Current Charge with Voltage Cutoff and TCO)
	Ni-MH Battery Charger (Constant-Current Timed Charge with TCO)
	Ni-MH Battery Charger (Constant-Current Charge with -dV and TCO)
	Ni-MH Battery Charger (Constant-Current Charge with dT°/dt and TCO)
	Ni-MH Battery Charger (Three-Step Charge with TCO)
	Battery Discharger (Constant-Current Timed Discharge with Voltage Cutoff)
Ni-MH Battery Charger (Constant-Current Charge with Voltage Cutoff and TCO)	
Charge Current	0-5 A
Cutoff Voltage	0-150 V
TCO	20-60°C (68-140°F)
Ni-MH Battery Charger (Constant-Current Timed Charge with TCO)	
Charge Current	0-5 A
Charge Duration	0-100 h
TCO	20-60°C (68-140°F)
Ni-MH Battery Charger (Constant-Current Charge with -dV and TCO)	
Charge Current	0-5 A
-dV	0-10 V
TCO	20-60°C (68-140°F)
Ni-MH Battery Charger (Constant-Current Charge with dT°/dt and TCO)	
Charge Current	0-5 A
dT°/dt	0-10°C/min (0-18°F/min)
TCO	20-60°C (68-140°F)
Ni-MH Battery Charger (Three-Step Charge with TCO)	
TCO	20-60°C (68-140°F)
Step-1 Current	0-5 A
Step-1 dT°/dt	0-10°C/min (0-18°F/min)
Step-2 Current	0-5 A
Step-2 Duration	0-100 min
Step-3 Current	0-5 A
Battery Discharger (Constant-Current Timed Discharge with Voltage Cutoff)	
Discharge Current	0-5 A
Discharge Duration	0-2000 min
Cutoff Voltage	0-150 V

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com