


Digital Circuit Fundamentals 2 FACET Board 581057 (91016-20)



LabVolt Series

Datasheet



Festo Didactic

en

10/2024

* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Table of Contents

General Description	3
Topic Coverage	3
Features & Benefits	3

General Description

The Digital Circuit Fundamentals 2 module is used to study and troubleshoot digital circuits using hands-on educational equipment.

Through the study of the following circuit blocks, students will gain the skills necessary to successfully troubleshoot specific circuit malfunctions:

- Clock
- Pulse Generator
- Counter
- Multiplexer/Demultiplexer
- BCD Decimal Decoder/BCD Priority Encoder
- ADC/DAC
- 7-Segment Driver/Display
- Parity Generator/ Checker

Topic Coverage

- Component Location and Identification
- Operation of General Circuits and IC Package Fundamentals
- Fundamentals: BCD Decoder Operation, Priority Encoder Operation, ADC Operation, DAC Operation
- Data Selector, Multiplexer, 1-Line-to-8-Line Demultiplexer
- 1-Line-to-8-Line Demultiplexer
- LED Decoder/Driver, 7-Segment LED Display, ODD and EVEN Parity
- ODD and EVEN Parity
- Parity Generator/Checker Glue Logic
- Troubleshooting Basics and Troubleshooting MSI IC Circuits and Digital Circuits

Features & Benefits

- +5 V regulated supply
- Built-in clock circuit
- Built-in pulse generator circuit
- Built-in counter circuitry

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com