

Two-Element Phasing Kit 581863 (9563-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
01/2025

Table of Contents

General Description	3
Manual	3
Specifications	3

General Description

The Two-Element Phasing Kit enables students to observe the effects of antenna phasing on the resulting antenna radiation pattern (combined radiation pattern). Different combined radiation patterns such as end-fire, broadside, and cardioid can be obtained. These can be measured, stored, and analyzed using the ATMS.



The Two Element Phasing Kit consists of an additional drooping monopole antenna (one is already included in the ATMS), an additional antenna mast with vertical mounting clips (one is already included in the ATMS), a power splitter/combiner, and a set of RF cables of different lengths. Phase shifts of 0, 90, and 180 degrees can be produced with the supplied RF cables. Other phase shifts can be produced by using RF cables having lengths that differ from those of the supplied RF cables.

Two drooping monopole antennas installed on the ATMS Antenna Positioner ready for experimenting the effects of antenna phasing.

Manual

Description

Manual number

Two Element Phasing Kit Instructions (User Guide) _____ 580352 (35166-E0)

Specifications

Parameter	Value
Operating Frequency	1 GHz
RF Cable Lengths	
RF Cable Lengths	30.0 (11.8 in)
	35.4 cm (13.9 in)
	40.8 cm (16.1 in)
Physical Characteristics	
Dimensions (H x W x D)	73 x 287 x 192 mm (2.9 x 11.3 x 7.6 in)
Net Weight	1.58 kg (3.4 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com