


QPSK/OQPSK/DPSK FACET Board 581201 (91029-20)

FESTO

LabVolt Series

Datasheet



Festo Didactic

en

05/2024

* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Table of Contents

General Description _____	3
ADDITIONAL FEATURES _____	3
Topic Coverage _____	3
Features & Benefits _____	4

General Description

Phase-shift keying (PSK) is a method of digital communication in which the phase of a transmitted signal is varied to convey information.

The QPSK/OQPSK/DPSK circuit board provides students with the theory and measurement skills required to implement and test different types of PSK modulation and demodulation techniques used in pulse-coded modulation (PCM) schemes.

The student first learns the principles and operational characteristics of unipolar and bipolar signals in a baseband transmission. Next, the student measures and compares BPSK, QPSK, OQPSK, and DPSK signals in the time and frequency domains using an oscilloscope and spectrum analyzer, respectively. Lastly, the student will become familiar with all components of the board; will be able to isolate, identify and test a series of circuits; and will perform troubleshooting exercises to demonstrate mastery of the course objectives.

The circuits found on this board include:

- NRZ Generator
- S/P Converter & Delay
- DPSK Encoder
- Power Supply/Regulator
- Channel Simulator
- Carrier & Phase Shift
- QPSK Modulator_I
- QPSK Modulator_Q
- Adder
- DPSK Decoder
- QPSK Demodulator_I
- QPSK Demodulator_Q
- Amplifier
- P/S Converter

ADDITIONAL FEATURES

- Communication signals are synchronized for easy display
- Digital signals observed in both time and frequency domains
- Courseware interfaces with the Virtual Instrument, Model 1250
- Built-in adjustable NRZ GENERATOR provides various bit pattern streams
- Adjustable bandwidth channel simulator

Topic Coverage

- Digital modulation
- Baseband signals, Passband signals
- Partitioning of pulse streams
- Signal constellations for MPSK, General Equations

- Heterodyning baseband signals with a carrier
- Unipolar and bipolar signals in time domain and in the frequency domain
- Binary PSK (BPSK), Quadratic PSK (QPSK), Offset QPSK (OQPSK), Differential PSK (DPSK) modulation and demodulation

Features & Benefits

- Communication signals are synchronized for easy display
- Digital signals observed in both time and frequency domains
- Courseware interfaces with the Virtual Instrument, Model 1250
- Built-in adjustable NRZ GENERATOR provides various bit pattern streams
- Adjustable bandwidth channel simulator

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com