

# Pneumatic Control Valve 582424 (46950-B0)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
11/2024

## Table of Contents

General Description _____	3
Manual _____	3
Table of Contents of the Manual(s) _____	3
Specifications _____	3

## General Description

The Pneumatic Control Valve is an industrial bronze control globe valve designed for pressure, flow, level, and temperature control applications. This reliable valve features a durable construction, tight shutoff, and good control characteristics. The valve is of the equal percentage type and is normally open.

This model includes a current-to-pressure converter which transforms a 4-20 mA input signal into a pneumatic output signal sent to the actuator of the control valve.

The Pneumatic Control Valve features a bypass that can be used to control the liquid flow manually.

## Manual

Description	Manual number
Control Valves (User Guide) _____	585145 (86001-E0)

## Table of Contents of the Manual(s)

### Control Valves (User Guide) (585145 (86001-E0))

- 1 Basic Control Valve Theory
- 2 Basic Control Valve (46950-B)
- 3 Pneumatic Control Valve with a Positioner (46950-A)
- 4 Control Valve with DVC2000 (46950-0)
- 5 Control Valve with DVC6000 – HART/FF (46950-E/-D)
- 6 Control Valve with DVC6200 – HART/FF (46950-E/-D)
- 7 Electric Control Valve (46950-C)

## Specifications

Parameter	Value
Input Signal	4-20 mA
Actuator Pressure Range	20-90 kPa (3-13 psi)
Type of valve	Globe, equal percentage, normally open

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

[www.labvolt.com](http://www.labvolt.com)

[www.festo-didactic.com](http://www.festo-didactic.com)