

# Basic Power Station 585673 (187-AP)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en 120 V - 60 Hz  
07/2025

Table of Contents

General Description \_\_\_\_\_ 3

Specifications \_\_\_\_\_ 3

## General Description

The Basic Power Station is ideal for use in classroom laboratories where science programs such as basic electricity, electronics, physics, and chemistry are taught. It has two variable-voltage ac outputs (high and low voltages), one fixed-voltage ac output, and one variable-voltage dc output (filtered). A control knob on the front panel sets the voltage of all variable outputs. Two standard grounding-type, simplex receptacles and a pair of color-coded banana jacks provide access to the ac power outputs. A pair of color-coded banana jacks provides access to the dc power output. The Basic Power Station is powered from a standard ac power outlet and turned on by a toggle switch on the front panel. A pilot light illuminates when the unit is energized.

The Basic Power Station is a handy portable unit that can be placed on any work surface in classroom laboratories. It is made of 16-gauge steel finished with scuff-resistant, black-baked enamel. The station is supplied complete with installation and operating instructions, one set of alligator-clip leads, and mounting hardware when required.

## Specifications

Parameter	Value
<b>Power Requirements</b>	
Current	10 A
Service Installation	Standard single-phase ac outlet
<b>Variable-Voltage DC Output</b>	
Voltage	0-12 V
Maximum Current	2.0 A
Ripple	Less than 10%
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Isolation	Floating, isolated from line and chassis grounds
<b>Fixed-Voltage AC Output</b>	
Voltage	120 V
Maximum Current	10 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
<b>Variable High-Voltage AC Output</b>	
Voltage	0-120 V
Maximum Current	1.0 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
<b>Variable Low-Voltage AC Output</b>	
Voltage	0-12 V
Maximum Current	2.0 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Isolation	Floating, isolated from line and chassis ground
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	190 x 146 x 170 mm (7.5 x 5.75 x 6.7 in)
Net Weight	3.9 kg (8.6 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**