

Basic Power Station 585674 (189-A0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en 120 V - 60 Hz
03/2025

Table of Contents

General Description	3
Specifications	3

General Description

The Basic Power Station, 189-A0, is ideal for use in classroom laboratories where science programs such as basic electricity, electronics, physics, and chemistry are taught. The Basic Power Station has two variable-voltage AC outputs (high and low voltages), one fixed-voltage AC output, and one variable-voltage DC output (filtered). A control knob on the front panel sets the voltage of all variable outputs. Two standard grounding-type, simplex receptacles and a pair of color-coded banana jacks provide access to the AC power outputs. A pair of color-coded banana jacks provides access to the DC power output. The Basic Power Station is powered from a standard AC power outlet and turned on by a toggle switch on the front panel. A pilot light illuminates when the unit is energized. It is recessed for semi-flush mounting in wood or metal rails using screws. To prevent tampering, it is assembled so that no screw heads or other means of component disassembly appear externally. The Basic Power Station is made of 16-gauge steel finished with scuff-resistant, black baked enamel. The station is supplied complete with installation and operating instructions, one set of alligator-clip leads, and mounting hardware when required.

Specifications

Parameter	Value
Power Requirements	
Current	10 A
Service Installation	Standard single phase outlet
Variable-Voltage DC Output	
Voltage	0 to 12 V
Maximum Current	2.0 A
Ripple	Less than 10%
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Isolation	Floating - isolated from line and chassis grounds
Fixed-Voltage AC Output	
Voltage	120 V
Maximum Current	10 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Variable High-Voltage AC Output	
Voltage	0 to 120 V
Maximum Current	1.0 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Variable Low-Voltage AC Output	
Voltage	0 to 12 V
Maximum Current	2.0 A
Overload Protection	Thermal-magnetic circuit breaker, trip and reset type
Isolation	Floating - isolated from line and chassis ground
Physical Characteristics	
Dimensions (H x W x D)	101 x 213 x 180 mm (4.0 x 8.75 x 7.1 in)
Dimensions (H x W) Cutout	92 x 187 mm (3.6 x 7.4 in)
Net Weight	3.5 kg (7.7 lb)
Clearances	177 mm (7 in) behind mounting surfaces
	25 mm (1 in) above unit

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com