

Pneumatic Control Valve (Air)

582428 (46953-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description	3
Manual	3
Table of Contents of the Manual(s)	3

General Description

The Pneumatic Control Valve for Air is a normally closed stainless steel valve with 1/4 inch connectors designed to regulate the flow of air. This compact valve features a rugged construction and good control characteristics over the air flow. The Pneumatic Control Valve (Air) includes a current-to-pressure converter which transforms a 4-20 mA input signal into a pneumatic signal sent to the actuator of the valve.

This control valve is available in different versions which can include a positioner. The various versions are:

- 46953-00 Pneumatic Control Valve (Air)
- 46953-A0 Pneumatic Control Valve for Air with Digital Positioner (HART) - DVC 2000
- 46953-B0 Pneumatic Control Valve for Air with a Positioner - Fisher 3660
- 46953-C0 Pneumatic Control Valve for Air with Digital Positioner (HART) - DVC 6200
- 46953-D0 Pneumatic Control Valve for Air with Digital Positioner (FOUNDATION Fieldbus) - DVC 6200

Manual

Description	Manual number
Control Valves (User Guide) _____	585145 (86001-E0)

Table of Contents of the Manual(s)

Control Valves (User Guide) (585145 (86001-E0))

- 1 Basic Control Valve Theory
- 2 Basic Control Valve (46950-B)
- 3 Pneumatic Control Valve with a Positioner (46950-A)
- 4 Control Valve with DVC2000 (46950-0)
- 5 Control Valve with DVC6000 – HART/FF (46950-E/-D)
- 6 Control Valve with DVC6200 – HART/FF (46950-E/-D)
- 7 Electric Control Valve (46950-C)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com