

# PID Controller

## 587021 (9034-00)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
03/2025

## Table of Contents

<b>General Description</b>	<b>3</b>
<b>Specifications</b>	<b>3</b>

## General Description

The P.I.D. Controller is designed to be used as a core unit in the implementation of control systems containing analog feedback loops. It contains a P.I.D. (Proportional, integral, Derivative) amplifiers section which is used to condition the analog control signal with proportional, integral and derivative effect. The gain of each of these amplifiers can be varied independently to control these effects.

The other sections include circuit elements to achieve feedback signal amplification, signal rectification, low-pass filtering, error detection and output signal summation and limiting. The limiting section includes an “Anti-Reset” circuit which prevents the integrating amplifier in the P.I.D. Amplifier’s section from saturating. All these elements can easily be interconnected through the use of miniature 2 mm banana plug connection leads.

## Specifications

Parameter	Value
<b>Rating (All Sections)</b>	
DC Power Input	±15 V, 100 mA
Input Voltage	0 to ±12 V
Output Voltage	0 to ±12 V
Input Impedance	1 MΩ
Output Impedance	1 kΩ
<b>Feedback amplifiers</b>	
Voltage Gain	1 to 10
<b>Low-Pass Filters</b>	
Voltage Gain	TTL compatible
Cut-off Frequency (Upper Filter)	0.2 Hz
Cut-off Frequency (Lower Filter)	0.2-70 Hz
<b>Error Detector</b>	
Number of Inputs	3 (1 inverted, 2 non-inverted)
Voltage Gain (for each input)	1
<b>P.I.D. Amplifier</b>	
Proportional Gain (Low)	0.5-5
Proportional Gain (High)	5-50
Derivative Gain	0.005-0.5
Integral Gain	10-100
<b>Summing Amplifier</b>	
Voltage Gain	1
<b>Limiter</b>	
Output Voltage (Upper Limit)	0 to +14 V
Output Voltage (Lower Limit)	0 to -14 V
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	154 x 287 x 440 mm (6.1 x 11.3 x 17.3 in)
Net Weight	4.5 kg (9.9 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**