


# Electrodynamometer, Imperial Units 586856 (8911-00)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en 120 V - 60 Hz  
11/2024

# Table of Contents

General Description	3
Specifications	3

## General Description

The Electrodynamometer is made of a squirrel-cage rotor fitted in a dc-excited stator. Mechanical loading is achieved by increasing the stator field current, which generates eddy currents in the driven rotor. The stator is trunnion-mounted on ball bearings and rotates against a helicoidal spring to oppose braking torque.

The front-end bell is provided with a circular scale that indicates the torque developed. The circular scale is graduated in Imperial units (lbf-in). A damper lever is located underneath the dynamometer to prevent oscillation if the power supply is applied while the dynamometer is turning. To measure the torque, this lever can be pushed to adjust and read the torque. The Electrodynamometer is electrically powered from standard fixed ac line supply.

The Electrodynamometer can be coupled to a 0.2 kW drive motor through the use of the Timing Belt, Model 8942. The faceplate can be lowered to provide access to the inside for coupling the Electrodynamometer to the drive motor. When closed, the faceplate is secured by two quick-lock fasteners.

A variant of the model expressing values in the International System of Units (SI) is also available (see Model 8911-1).

## Specifications

Parameter	Value
<b>Rating</b>	
Torque Range (8911)	-3 to +27 lbf-in
Speed	250 to 3000 r/min
Accuracy	2%
Input Voltage	120 V – AC
Input Current	2 A
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	308 x 291 x 490 mm (12.1 x 11.5 x 19.3 in)
Net Weight	17.4 kg (38.3 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**