

**Bench (Assembled, with Dressing Panels and  
Lockable Front Door)**  
587929 (6303-C0)

**FESTO**

**LabVolt Series**

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
05/2025

## Table of Contents

<b>General Description</b>	<b>3</b>
<b>Specifications</b>	<b>3</b>

## General Description

The Bench (with Dressing Panels and Lockable Front Door, Assembled) consists of a mobile workstation on which the Work Surfaces, Models 6301 and 6301-1, can be mounted. Four heavy-duty, swiveling, lockable casters allow the bench to be easily moved in the laboratory classroom. The bench has three pairs of side supports over which three Storage/Work Surfaces, Model 6309, can be slid to provide shelving for component storage.

This bench variant is provided already assembled and comprises dressing panels with a lockable front door. These dressing panels fully enclose the bench. The lockable front door consists of two hinged panels with a lock handle to secure the content of the bench.

## Specifications

Parameter	Value
<b>Physical Characteristics</b>	
Intended Location	On the floor (stands on casters)
Dimensions (H x W x D)	910 x 850 x 660 mm (35.8 x 33.5 x 26 in)
Net Weight	64 kg (141 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**