


# Paddle Wheel Flow Transmitter 588222 (6542-00)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
11/2024

## Table of Contents

General Description	3
Specifications	3

## General Description

The Paddle Wheel Flow Transmitter is a paddle wheel flow transmitter with two outputs controlled using 0-5 V dc or 4-20 mA signals. The first output is a voltage output calibrated at 1 V per l/min (3.85 V per gal US/min). The second output is a frequency output calibrated at 22.1 Hz per l/min (85 Hz per gal US/min).

The Paddle Wheel Flow Transmitter has a span adjustment of 7-9.5 l/min (1.8-2.5 gal US/min), a linearity of  $\pm 1.5\%$  of the full scale, a maximum pressure of 175 kPa (25 psig), and an operating temperature of 5-70°C (41-158°F). The supply voltage of the Paddle Wheel Flow Transmitter is 24 V dc.

## Specifications

Parameter	Value
<b>Supply Voltage</b>	24 V dc
<b>Outputs</b>	
Control	0-5 V dc, 4-20 mA
Calibrated	Two, one voltage output of 1 V per L/min (3.85 V per gal US/min), and 0-5 V frequency output of 22.1 Hz per L/min (85 Hz per gal US/min).
<b>Span Adjustment</b>	7-9.5 L/min (1.8-2.5 gal US/min)
<b>Linearity</b>	$\pm 1.5\%$ of full scale
<b>Maximum Pressure</b>	175 kPa (25 psig)
<b>Operating Temperature</b>	5-70°C (41-158°F)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

[www.labvolt.com](http://www.labvolt.com)

[www.festo-didactic.com](http://www.festo-didactic.com)