


FactoryTalk View ME Studio (Educational) 588384 (46968-00)

FESTO

LabVolt Series

Datasheet



Festo Didactic
en
11/2024

* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Table of Contents

General Description	3
Manual	3
Specifications	3

General Description

FactoryTalk View is a Windows-based application suite, produced by Rockwell Software, which simplifies the creation of graphic human-machine interfaces (HMI), such as operator interface solutions, to monitor and control machines and small processes. This versatile suite is compatible with a wide array of PLCs constitutes a distributed control system development solution of choice.

HMI applications are developed and edited using FactoryTalk View Studio, which also has limited runtime capabilities to test your interface. A completed application can be loaded directly on a Touch Screen Graphic Terminal, Model 5922 or 46973, as it includes a built-in runtime software. Your applications can also be designed to run on a computer, but doing so requires the purchase of FactoryTalk View Machine Edition Station Runtime.

Available versions:

- 46968-0 FactoryTalk View ME Studio (Educational)
- 46968-2 FactoryTalk View ME Station (Educational)
- 46968-A FactoryTalk View ME Studio (Commercial)
- 46968-C FactoryTalk View ME Station (Commercial)

Manual

Description	Manual number
Human-Machine Interfaces (User Guide)	585116 (85985-E0)

Specifications

Parameter	Value
Computer Requirements	A currently available personal computer running under one of the following operating systems: Windows® 7 or Windows® 8.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com