

pH Process Control Accessories

588244 (6591-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The pH Process Control Accessories, Model 6591, includes the following:

- Laboratory glassware
- Two beakers, one with 100-ml (3.4-oz) capacity and one with 600-ml (20.3-oz) capacity
- Two graduated cylinders, one with 100-ml (3.4-oz) capacity and one with 10-ml (0.3oz) capacity
- Volumetric flask with a 2000-ml (67.63-oz) capacity
- Two chemical splash goggles
- Tubing and hoses connectors
- Spatula
- Column cap
- Dropping bottle
- Disposable transfer pipettes
- Current calibrator
- Precision scale
- Two funnels
- 2 mm plugs
- Tubing holder

Specifications

Parameter	Value
Laboratory Glassware	
Beaker	Two, one with 100 ml (3.4 oz) capacity and one with 600 ml (20.3 oz) capacity
Graduated Cylinder	Two, one with 100 ml (3.4 oz) capacity and one with 10 ml (0.3 oz) capacity
Volumetric Flask	2000 ml (67.63 oz) capacity
Miscellaneous	
Includes:	Chemical splash goggles (2)
	Tubing and hoses connectors
	Spatula
	Column cap
	Dropping bottle
	Disposable transfer pipettes
	Current calibrator
	Precision scale
	Funnels (2)
	2 mm plugs
	Tubing holder

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com