

Ultrasonic Level Transmitter (HART) 588337 (46930-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description _____	3
List of Manuals _____	3
Table of Contents of the Manual(s) _____	3

General Description

The Ultrasonic Level Transmitter is a level measurement device that uses sound waves to detect the level of liquid in the column of the Pressure, Flow, Level, and Temperature Process Training Systems. The Ultrasonic Level Transmitter includes an ultrasonic sensor/emitter installed on the flange of the column and a transmitter supporting either the HART or FOUNDATION field bus communication protocols. The Ultrasonic Level Transmitter can be configured manually, but it is strongly recommended to use the optional Software Configurator, Model 46982, to simplify and render more efficient the process of configuring advanced echo parameters.

The Ultrasonic Level Transmitter is a noncontact sensor. In the industry it is usually used in corrosive environments. Changes in the density, conductivity, and composition of the process fluid do not affect this sensor.

Available Ultrasonic Level Transmitters:

- 46930-0 Ultrasonic Level Transmitter (HART)
- 46930-A Ultrasonic Level Transmitter (FOUNDATION Fieldbus)

List of Manuals

Description	Manual number
Ultrasonic Level Transmitter (HART) (Workbook) _____	585127 (85991-00)
Ultrasonic Level Transmitter (HART) (Workbook (Instructor)) _____	585128 (85991-10)

Table of Contents of the Manual(s)

Ultrasonic Level Transmitter (HART) (Workbook) (585127 (85991-00))

- 1 Familiarization and Basic Level Measurement
- 2 Troubleshooting

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com