

Dual-Sided Instrumentation Workstation

589003 (6305-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
04/2025

Table of Contents

General Description	3
Features & Benefits	3
Specifications	3

General Description

The Instrumentation Workstation is designed to house devices such as controllers, PLC's, Color Paperless Recorders, and Touch Screen Graphic Terminals. The workstation allows two student groups to work simultaneously. This prevents the equipment from coming in contact with water.

It features two Instrumentation Mounting Pipes to install instruments, usually differential-pressure transmitters, at the appropriate height and close to the point of measurement. The mounting pipe replicates the common industrial practice of installing a measuring instrument directly on the process pipe or on an adjacent one.

The structure is pre-assembled, made of steel, and intended for use on a table (not supplied, offered as option). Four pairs of mounting rails firmly hold the modules of the Process Automation line of products in place. One holder on each side permits users to neatly arrange the test leads. A touch-screen computer mount (not supplied, offered as option) can be attached to either side.

Features & Benefits

- The workstation makes it possible to expand the 6090 Process Control System with the PLC'S, recorders and transmitters according to instructor's training program. It is very cost effective because two teams can work simultaneously.

Specifications

Parameter	Value
Dimensions	
(HxWxD)	976x1041x484

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com