

Numerical Distance Relay (with safe connections) 589111 (3813-A0)

FESTO

LabVolt Series

Datasheet



Table of Contents

General Description	2
List of Manuals	3
Optional Manual(s)	3
Specifications	3

General Description

The Numerical Distance Relay is a power-utility grade, numerical protective relay (Siemens SIPROTEC 5 series) mounted in a table-top enclosure. The relay can perform the protection functions listed below.

- Phase distance (21) protection
- Ground distance (21N) protection
- Directional phase overcurrent (67) protection
- Directional ground overcurrent (67N) protection
- Directional power (32) protection
- Instantaneous phase overcurrent (50) protection
- Instantaneous ground overcurrent (50N) protection
- Phase overcurrent (51) protection
- Ground overcurrent (51N) protection
- Machine or transformer thermal (49) protection

The Numerical Distance Relay can also perform several other standard protection functions (ANSI 27, 37, 38, 46, 59, 68, 74, 81, 86, and 87N).

The front panel of the relay includes connections to all inputs, outputs and ports and features a display that can provide information about the relay protection functions, indicate numerous currently measured values such as the line voltages, line currents, phase power, three-phase power, and power factor, and show information about trip events that have been recorded. A keypad, also on the front panel of the relay, allows users to select the information displayed. The front panel of the relay also features a set of 16 LEDs that allows quick monitoring of the status of various relay functions.

Relay programming (e.g., protection function selection, function settings) is achieved via the Siemens DIGSI 5 software. This software is designed to be run from a personal computer with a Microsoft® Windows™ operating system. Communication between the computer and the relay is through a USB port or an Ethernet port. Relay function settings can also be performed using the keypad and display located on the front panel of the relay. Once programmed, the Numerical Distance Relay can be tested using a built-in relay testing unit to ensure it is programmed to operate as expected. This eliminates the need for users to purchase a costly external relay tester to perform relay testing. The built-in relay testing unit is operated using the DIGSI 5 software.

Access to the voltage and current inputs of the Numerical Distance Relay is through a removable panel located at the back of the relay enclosure. Access to the relay Ethernet port, binary inputs, and binary outputs (e.g., trip

contacts) is also through this removable panel. The Numerical Distance Relay is powered via an ac power inlet mounted on the front of the relay enclosure.

List of Manuals

Description	Manual number
Numerical Protective Relays (User Guide) _____	590108 (52766-E0)
Numerische Schutzrelais (User Guide) _____	593908 (52766-EG)
Relais de protection numériques (User Guide) _____	593909 (52766-E1)
Relés numéricos de protección (User Guide) _____	593910 (52766-E2)

Optional Manual(s)

Qty	Description	Model number
1	Overcurrent and Overload Protection Using Protective Relays (Student Manual) _____	589887 (52173-00)
1	Overcurrent and Overload Protection Using Protective Relays (Instructor Guide) _____	589888 (52173-10)
1	Directional Protection (Student Manual) _____	589889 (52174-00)
1	Directional Protection (Instructor Guide) _____	589890 (52174-10)
1	Distance Protection (Student Manual) _____	593880 (52176-00)
1	Distance Protection (Instructor Guide) _____	593881 (52176-10)

Specifications

Parameter	Value
Relay	
Type	Siemens 7SA82
Power Requirements	
Voltage	100-240 V
Apparent Power	35 VA
Frequency	50/60 Hz
Input	IEC C14 input on the front panel
Protection	6 A circuit breaker
Computer Interface	
Connection	RJ45 EtherNet port on the front panel
Software	DIGSI 5 Software included, free license for educational institutions obtainable from Siemens via application
Physical Characteristics	
Intended Location	On a work surface able to support the weight of the equipment, or on a Festo-approved A4 workstation or equivalent
Dimensions (H x W x D)	295 x 400 x 240 mm (11.61 x 15.75 x 9.45 in)
Net Weight	9.1 kg (20.0 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2020. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com