

Capacitive Load 594822 (8331-PC)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en 230 V - 50 Hz
10/2021

Table of Contents

General Description	2
Specifications	2

General Description

The Capacitive Load consists of a module housing nine capacitors arranged in three identical banks. Each bank consists of three capacitors connected in parallel that can be switched on or off with toggle switches to obtain various capacitance values. This allows the equivalent capacitance of each bank to be increased or decreased by steps. Six safety banana jacks on the module front panel provide access to each capacitor bank. The three capacitor banks can be connected separately for operation in three-phase circuits. Also, the three capacitor banks can be connected together for operation in single-phase circuits.

A permanently connected discharge resistor reduces the voltage across the terminals of each bank of capacitors to 5% of the applied voltage within 25 seconds after the load is disconnected from the supply. The Capacitive Load may be used with both dc and ac power.

The Capacitive Load is commonly used in conjunction with the other basic load modules, the Resistive Load and the Inductive Load to experiment with the effects of different types of load on a circuit.

Specifications

Parameter	Value
Capacitors	
Quantity	Three identical banks of three capacitors
Capacitance Values (Each Bank)	0,72/1,45/2,89 μF
Reactance Values (Each Bank)	1100/2200/4400 Ω
Nominal Voltage	230 V – 50 Hz
Maximum Voltage	440 V
Capacitance Value Accuracy	$\pm 5\%$
Load at Nominal Voltage (Each Bank)	
Reactive Power	84 var
Current	0,523-0,366 A
Steps	Seven, of equal increment
Current Increment	0,523 A
Conformity/Directives	CE and RoHS
Physical Characteristics	
Dimensions (H x W x D)	297 x 266 x 140 mm
Net Weight	2,7 kg

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2021. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com