


Three-Way Pneumatic Control Valve with Digital Positioner (HART) - DVC 6200 588376 (46955-E0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en 120 V - 60 Hz
11/2024

Table of Contents

General Description _____	3
Manual _____	3
Table of Contents of the Manual(s) _____	3

General Description

The Three-Way Control Valve is an industrial bronze control globe valve designed mainly for temperature control applications. This reliable valve features a durable construction, tight shutoff, and good control characteristics. The valve is designed to be used in mixing mode (two inlets, one outlet) and is of equalpercentage type. This valve is normally open on the lower port.

Like the Control Valve, Model 46950-X, this model has either a pneumatic or an electric actuator and may feature options such as a digital valve controller (either a DVC 2000 or a DVC 6200) supporting either HART or Fieldbus, or a pneumatic positioner. Refer to the description of the equivalent 46950-X model for more information.

- 46955-0 Three-Way Pneumatic Control Valve with Digital Positioner (HART) - DVC 2000
- 46955-A Three-Way Pneumatic Control Valve with Positioner (Fisher 3660)
- 46955-B Three-Way Pneumatic Control Valve
- 46955-C Three-Way Electric Control Valve
- 46955-D Three-Way Pneumatic Control Valve with Digital Positioner (FOUNDATION Fieldbus) - DVC 6000
- 46955-E Three-Way Pneumatic Control Valve with Digital Positioner (HART) - DVC 6000

Manual

Description

Manual number

Control Valves (User Guide) _____ 585145 (86001-E0)

Table of Contents of the Manual(s)

Control Valves (User Guide) (585145 (86001-E0))

- 1 Basic Control Valve Theory
- 2 Basic Control Valve (46950-B)
- 3 Pneumatic Control Valve with a Positioner (46950-A)
- 4 Control Valve with DVC2000 (46950-0)
- 5 Control Valve with DVC6000 – HART/FF (46950-E/-D)
- 6 Control Valve with DVC6200 – HART/FF (46950-E/-D)
- 7 Electric Control Valve (46950-C)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com