

# Numerical Directional Overcurrent Relay (with safe connections) 589110 (3812-A0)

**FESTO**

LabVolt Series

Datasheet



Festo Didactic  
en  
01/2025

\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

## Table of Contents

<b>General Description</b>	<b>3</b>
<b>Courseware</b>	<b>3</b>
<b>List of Manuals</b>	<b>3</b>
<b>Additional Equipment Required to Perform the Exercises (Purchased separately)</b>	<b>4</b>
<b>Optional Manual(s)</b>	<b>4</b>
<b>Specifications</b>	<b>4</b>

## General Description

The Numerical Directional Overcurrent Relay is a power-utility grade, numerical protective relay (Siemens SIPROTEC 5 series) mounted in a table-top enclosure. The relay can perform the protection functions listed below.

- Directional phase overcurrent (67) protection
- Directional ground overcurrent (67N) protection
- Directional power (32) protection
- Instantaneous phase overcurrent (50) protection
- Instantaneous ground overcurrent (50N) protection
- Phase overcurrent (51) protection
- Ground overcurrent (51N) protection
- Machine or transformer thermal (49) protection

The Numerical Directional Overcurrent Relay can also perform several other standard protection functions (ANSI 27, 37, 38, 46, 59, 74, 81, 86, and 87N).

The front panel of the relay features a display that can provide information about the relay protection functions, indicate numerous currently measured values such as the line voltages, line currents, phase power, three-phase power, and power factor, and show information about trip events that have been recorded. A keypad, also on the front panel of the relay, allows users to select the information displayed. The front panel of the relay also features a set of 16 LEDs that allows quick monitoring of the status of various relay functions.

Relay programming (e.g., protection function selection, function settings) is achieved via the Siemens DIGSI 5 software. This software is designed to be run from a personal computer with a Microsoft® Windows™ operating system. Communication between the computer and the relay is through a USB port or an Ethernet port. Relay function settings can also be performed using the keypad and display located on the front panel of the relay. Once programmed, the Numerical Directional Overcurrent Relay can be tested using a built-in relay testing unit to ensure it is programmed to operate as expected. This eliminates the need for users to purchase a costly external relay tester to perform relay testing. The built-in relay testing unit is operated using the DIGSI 5 software.

## Courseware

Numerical protection relay	Available courses (each including a student manual and an instructor guide)			
	Overcurrent and Overload Protection Using Protective Relays Manual 52173	Directional Protection Manual 52174	Differential Protection Manual 52175	Distance Protection Manual 52176
3812	X	X		
3813	X	X		X
3819	X		X	

Different courses are available to perform exercises using the Numerical Directional Overcurrent Relay. Each course consists of a student manual providing comprehensive theory presentations, guided, easy-to-

understand lab procedures, and review questions. Each course also comprises an instructor guide that includes both the content of the student manuals as well as the results and answers to questions.

The following table indicates which courses are available for each numerical protective relay.

## List of Manuals

Description	Manual number
Numerical Protective Relays (User Guide) _____	590108 (52766-E0)
Numerische Schutzrelais (User Guide) _____	593908 (52766-EG)

**Description****Manual  
number**

Relais de protection numériques (User Guide) \_\_\_\_\_ 593909 (52766-E1)  
 Relés numéricos de protección (User Guide) \_\_\_\_\_ 593910 (52766-E2)

**Additional Equipment Required to Perform the Exercises (Purchased separately)****Qty Description****Model  
number**

1 License for DIGSI 5 Premium Software \_\_\_\_\_ 779959 (52286-00) <sup>1</sup>

**Optional Manual(s)****Qty Description****Model  
number**

1 Overcurrent and Overload Protection Using Protective Relays (Workbook) \_\_\_\_\_ 589887 (52173-00)  
 1 Overcurrent and Overload Protection Using Protective Relays (Workbook (Instructor)) \_\_\_\_\_ 589888 (52173-10)  
 1 Directional Protection (Workbook) \_\_\_\_\_ 589889 (52174-00)  
 1 Directional Protection (Workbook (Instructor)) \_\_\_\_\_ 589890 (52174-10)

**Specifications**

Parameter	Value
Relay Type	Siemens 7SJ82
<b>Power Requirements</b>	
Voltage	100-240 V
Apparent Power	35 VA
Frequency	50/60 Hz
Input	IEC C14 input on the front panel
Protection	6 A circuit breaker
<b>Computer Interface</b>	
Connection	RJ45 EtherNet port on the front panel
Software	DIGSI 5 Software included, free license for educational institutions obtainable from Siemens via application
<b>Physical Characteristics</b>	
Intended Location	On a work surface able to support the weight of the equipment, or on a Festo-approved A4 workstation or equivalent
Dimensions (H x W x D)	295 x 400 x 240 mm (11.61 x 15.75 x 9.45 in)
Net Weight	7.08 kg (15.6 lb)

<sup>1</sup> This license is intended only for the non-educational customers. For educational customer, the software is provided for free with a 10 users license. No need to add this additional part number in the order.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**