

Radar Transmitter 595172 (9620-20)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The Radar Transmitter is an instructional module designed to provide training in system- and module-level troubleshooting. It has switches that the instructor can use to insert faults. These switches, as well as the circuit boards and test points, are accessed through the hinged door on top of the module.

The Radar Transmitter generates an RF signal that can be either frequency modulated or amplitude modulated. It includes an RF oscillator, a pulse generator, and an amplitude modulator.

The RF oscillator has a frequency modulator with variable modulation frequency and deviation. It also has a variable output frequency, which is indicated on 2½ digit display. An RF power switch allows the RF output to be disabled.

The pulse generator produces the pulses required by the system. It provides discrete and continuous variation of the pulse width. The pulse generator output signal controls the amplitude modulator to produce the pulsed (amplitude-modulated) RF signal.

Unregulated dc power is automatically supplied to the Radar Transmitter through self-aligning connectors when it is installed on the Power Supply / Antenna Motor Driver.

Specifications

Parameter	Value
RF Oscillator	
Frequency Range	8 to 10 GHz
Output Power	+10 dBm (typical)
Output Impedance	50 Ω
CW/FM-CW RF Output	
Power	+0.5 dBm (typical)
Impedance	50 Ω
Pulse Generator	
Pulse Width Ranges	1, 2, 5, 1 to 5 ns
Trigger Input	TTL
Output Level	300 mV
Output Impedance	50 Ω
Faults	10, switch-insertable
Test Points	10
Physical Characteristics	
Dimensions (H x W x D)	162 x 330 x 300 mm (6.4 x 13 x 11.8 in)
Net Weight	5 kg (11 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com