

Time-Delay Relay
595976 (3132-40)



LabVolt Series

Datasheet



Code	Function
A	ON-delay
B	OFF-delay
C	ON-delay with control signal
D	Flasher relay, symmetrical, starting with control signal
E	Passing make contact, interval relay
F	Retriggerable interval relay with deactivated control signal
G	Passing make contact with control signal, not retriggerable
H	Additive ON-delay, not retriggerable, instantaneous OFF
I	Additive ON-delay with control signal
J	Flasher relay, symmetrical, starting with control signal
K	Pulse-delay relay, fixed pulse (1 s) and settable pulse delay
L	Pulse-delay relay with control signal
M	Retriggerable interval relay with activated control signal

Rating
Coil: 12-240 V 50/60 Hz
Aux. Voltage: 12-240 V 50/60 Hz
Contacts: 3 A 250 V 50/60 Hz

* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The Time Relay consists of a multifunction time relay with multiple ranges, one normally open contact and one normally closed contact. The relay enables the implementation of a large variety of functions.

Specifications

Parameter	Value
Coil	
	12-240 V - DC/AC (50/60 Hz)
Range	
	0.05 s - 100 h (multiple ranges)
Functions (13)	
A	On-delay
B	OFF-delay with control signal
C	ON-delay and OFF-delay with control signal
D	Flasher relay, symmetrical, starting with interval
E	Passing make contact, interval relay
F	Retriggerable interval relay with deactivated control signal
G	Passing make contact with control signal, not retriggerable
H	OFF-delay with control signal
I	Additive ON-delay, not retriggerable, with control signal
J	Flasher relay, symmetrical, starting with pulse
K	Pulse-delay relay, fixed pulse (1 s) and settable pulse delay
L	Pulse-delay relay with control signal
M	Retriggerable interval relay with activated control signal
Contacts	
AC-15	3A - 250 V - 50/60 Hz
DC-13	1 A at 24 V, 0.2 A at 125 V and 0.1 A at 250 V
Physical Characteristics	
Dimensions (H x W x D)	203 x 153 x 172 mm (8 x 6 x 6.8 in)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com