


Guided-Radar Level Transmitter (Bluetooth, Heartbeat, HART) 611545 (46932-40)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
04/2025

Table of Contents

General Description	3
List of Manuals	3
Table of Contents of the Manual(s)	3

General Description

The Guided-Radar Level Transmitter is a level measurement device using electromagnetic waves to detect the level of liquid in the column of the Pressure, Flow, Level, and Temperature Process Training Systems. Changes in the density, conductivity, and composition of the process fluid do not affect this sensor. The Guided-Radar Level Transmitter includes a rod probe to guide the signal in the column and a transmitter supporting either the HART communication protocol. The device can be configured manually via its alphanumeric display and push-buttons, but as it is difficult to efficiently program the transmitter's advanced functions on the device's display, acquiring a Software Configurator, Model 46982, is required.

Available Guided-Radar Level Transmitters:

- 46932-0 Guided-Radar Level Transmitter (HART)
- 46932-4 Guided-Radar Level Transmitter (Bluetooth, Heartbeat, HART)

List of Manuals

Description	Manual number
Radar Level Transmitters (Workbook) _____	589760 (52200-00)
Radar Level Transmitters (Workbook (Instructor)) _____	589762 (52200-10)

Table of Contents of the Manual(s)

Radar Level Transmitters (Workbook) (589760 (52200-00))

- 1 Fundamentals of Radar Level Transmitters

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com