

TIA Portal PLC Software (Step 7 Professional, WinCC) 5939

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
04/2025

Table of Contents

General Description	3
List of Available Training Systems	3
Equipment Description	3

General Description

The TIA Portal PLC Software includes Step 7 Professional and WinCC Software. Step7 is a programming software that is required for programming Siemens programmable logic controllers.

WinCC is the engineering tool for project planning of SIMATIC HMI operator units and the PC-based visualization systems.

List of Available Training Systems

Qty	Description	Model number
1	PLC Software (Step 7 Professional / WinCC) - 1 User	587904 (5939-00)

Equipment Description

PLC Software (Step 7 Professional / WinCC) - 1 User 587904 (5939-00)



The PLC Software (Step 7 Professional) is a programming software that is required for programming Siemens programmable logic controllers.

Specifications

Parameter	Value
Software	Step 7 Professional
Features	Designed for SIMATIC [®] controllers, Step 7 allows programming in LAD, FBD, and STL languages. It also includes tools for graphic and high-level language programming.
Computer Requirements	A currently available personal computer Pentium type with RS-232 serial port, running under one of the Microsoft [®] operating systems, Windows [®] 2000, Windows [®] XP, Windows [®] Vista or Windows [®] 7, is required.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com