

pH multiparameter transmitter (Heartbeat, HART) 611546 (46947-40)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
05/2025

Table of Contents

General Description_____ **3**

General Description

The pH transmitter features a pH probe which measures the electrochemical potential of a solution to determine its pH. The transmitter displays the pH measured by the probe and has a 4-20 mA output to transmit the measurement to a controller. The transmitter supports the HART communication protocol.

This multiparameter analytic transmitter features four digital sensor inputs and four analog outputs. The Heartbeat technology permits to monitor and verify the instrument and the probes health status.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com