

# Inductive Load 594821 (8321-PC)

# FESTO

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en 230 V - 50 Hz  
10/2021

## Table of Contents

General Description	2
Specifications	2

### General Description

The Inductive Load consists of a module housing nine iron-core power inductors arranged in three identical banks. Each bank consists of three inductors connected in parallel that can be switched on or off with toggle switches to obtain various inductance values. This allows the equivalent inductance of each bank to be increased or decreased by steps. Six safety banana jacks on the module front panel provide access to each inductor bank. The three inductor banks can be connected separately for operation in three-phase circuits. Also, the three inductor banks can be connected together for operation in single-phase circuits.

The Inductive Load is commonly used in conjunction with other basic load modules, like the Resistive Load and the Capacitive Load to experiment with the effects of different types of load on a circuit.

### Specifications

Parameter	Value
<b>Inductors</b>	
Quantity	Three identical banks of three inductors
Inductance Values (Each Bank)	3,5/7/14 H
Reactance Values (Each Bank)	1100/2200/4400 $\Omega$
Nominal Voltage	230 V – 50 Hz
Inductance Value Accuracy	$\pm 5\%$
<b>Load at Nominal Voltage (Each Bank)</b>	
Reactive Power	84 var
Current	0,523 - 0,366 A
Steps	Seven, of equal increment
Current Increment	0,523 A
<b>Conformity/Directives</b>	CE and RoHS
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	297 x 266 x 140 mm
Net Weight	9 kg

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2021. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

[www.labvolt.com](http://www.labvolt.com)

[www.festo-didactic.com](http://www.festo-didactic.com)