

# Time-Delay Relay 595976 (3132-40)

# FESTO

LabVolt Series

Datasheet



Festo Didactic  
en  
11/2024

\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

## Table of Contents

|                           |   |
|---------------------------|---|
| General Description _____ | 3 |
| Specifications _____      | 3 |

## General Description

The Time Relay consists of a multifunction time relay with multiple ranges, one normally open contact and one normally closed contact. The relay enables the implementation of a large variety of functions.

## Specifications

| Parameter                       | Value   |
|---------------------------------|---|
| <b>Coil</b>                     |   |
|                                 | 12-240 V - DC/AC (50/60 Hz)                                   |
| <b>Range</b>                    |   |
|                                 | 0.05 s - 100 h (multiple ranges)                              |
| <b>Functions (13)</b>           |   |
| A                               | On-delay  |
| B                               | OFF-delay with control signal                                 |
| C                               | ON-delay and OFF-delay with control signal                    |
| D                               | Flasher relay, symmetrical, starting with interval            |
| E                               | Passing make contact, interval relay                          |
| F                               | Retriggerable interval relay with deactivated control signal  |
| G                               | Passing make contact with control signal, not retriggerable   |
| H                               | OFF-delay with control signal                                 |
| I                               | Additive ON-delay, not retriggerable, with control signal     |
| J                               | Flasher relay, symmetrical, starting with pulse               |
| K                               | Pulse-delay relay, fixed pulse (1 s) and settable pulse delay |
| L                               | Pulse-delay relay with control signal                         |
| M                               | Retriggerable interval relay with activated control signal    |
| <b>Contacts</b>                 |   |
| AC-15                           | 3A - 250 V - 50/60 Hz   |
| DC-13                           | 1 A at 24 V, 0.2 A at 125 V and 0.1 A at 250 V                |
| <b>Physical Characteristics</b> |   |
| Dimensions (H x W x D)          | 203 x 153 x 172 mm (8 x 6 x 6.8 in)                           |

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

[www.labvolt.com](http://www.labvolt.com)

[www.festo-didactic.com](http://www.festo-didactic.com)