

# Dual-Channel Sampler 595989 (9605-10)

**FESTO**

LabVolt Series

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
11/2024

## Table of Contents

General Description _____	3
Specifications _____	3

## General Description

The Dual-Channel Sampler performs time expansion of the I- and Q-channel baseband signals from the radar receiver in order to allow further processing and display. It has three switches to select the system observation range, as well as control knobs for adjusting the system range origin, the balance of the I- and Q-channel output signals, and the DC offsets at the I- and Q-channel outputs. A time base output is provided to obtain an A-scope display on a conventional oscilloscope.

Unregulated DC power is automatically supplied to the Dual-Channel Sampler through self-aligning connectors when it is installed on the Power Supply / Antenna Motor Driver

## Specifications

Parameter	Value
I-, Q-Channel Input Voltage Range	-1 V to +1 V
Pulse Input Impedance	50 $\Omega$
Trigger Inputs	TTL
Range	Selectable, 1.8, 3.6, and 7.2 m (5.9, 11.8, and 23.6 ft)
A-Scope Time-Base Output Level	2 V

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**