

Power Supply / Antenna Motor Driver 8084743 (9601-20)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The Power Supply / Antenna Motor Driver is the physical base for the Basic Radar Training System. Several modules of the system are designed to be stacked on top of it, side-by-side. The power supply distributes three unregulated dc voltages to the stacked modules through self-aligning connectors. These voltages are regulated within each module to provide the required voltages. Three regulated dc voltage outputs are also available through miniature banana jacks on the front panel of the power supply.

The antenna motor driver supplies power to the Rotating-Antenna Pedestal. It is a Pulse-Width-Modulated (PWM) motor driver that uses a four-quadrant chopper requiring a command signal from the antenna controller or radar target tracking system. It is equipped with front-panel test points for training purposes.

Specifications

Parameter	Value
Power Requirement	
Current	
Service Installation	Standard single-phase ac outlet
Power Supply	
Unregulated DC Outputs	-25 V typ. -3 A max.; +11 V typ. - 5 A max. (two separate outputs); +25 V typ. - 3 A max.
Regulated DC Outputs	-15 V at 0.5 A; +5 V at 1 A; + 15 V at 0.5 A
AC Line Protection	
Regulated DC Output Protection	
Unregulated DC Output Protection	
Antenna Motor Driver	
Input Voltage Range	-10 to +10 V
PWM Output Voltage Range	-24 V to +24 V max.
Physical Characteristics	
Dimensions (H x W x D)	104 x 687 x 305 mm (4.1 x 27 x 12 in)
Net Weight	

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com