

AC 24V Power Supply 772050 (8826-PC)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en 230 V - 50 Hz
10/2021

Table of Contents

General Description	2
Specifications	2

General Description

The AC 24V Power Supply consists of a fixed-voltage 24 V power source enclosed in a module. The AC 24V Power Supply is used to power specific modules of the Electric Power Technology Training Systems, such as the Data Acquisition and Control Interface, the IGBT Chopper/Inverter, and the Power Thyristors.

Specifications

Parameter	Value
Module Requirements	
Maximum Current	0,3 A
AC Power Network Installation	230 V – 50/60 Hz, must include live, neutral, and ground wires
Outputs	
Fixed AC 1-Phase	24 V – 2,5 A
Conformity/Directives	CE and RoHS
Physical Characteristics	
Dimensions (H x W x D)	297 x 133 x 140 mm
Net Weight	2,8 kg

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2021. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com