

Smart Meter

8093902 (9057-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____ 3

Specifications _____ 3

General Description

The Smart Meter module is a compact power monitoring device designed for basic metering and energy monitoring. It is an entry-level solution for digital electrical metering, compared to the Data Acquisition and Control Interface which is the main measurement device used through our complete curriculum. It features a PAC3200 from Siemens, a powerful compact power monitoring device widely used in industrial and commercial metering and monitoring applications.

The Smart Meter provides access to multiple values being monitored such as voltage, current, power, power factor, frequency, THD, and energy consumption. For each value, users can read the RMS as well as average, minimum, and maximum values. Users navigate the user-friendly interface using the pushbuttons below the LCD screen.

The PAC3220 features two digital inputs and two digital outputs. It is also equipped with a communication port compatible with Ethernet and Modbus TCP via the RJ45 port on the front panel for integration with other devices.

Specifications

Parameter	Value
Measured Values	
Voltage	Phase-phase / phase-neutral
Currents	Per phase
Apparent, Active and Reactive Power	Per phase and total
Power Factor	Per phase and total
Frequency	45...64 Hz
THD for voltage and current	Per phase
Min. / max. values	Voltage (phase-phase, phase-neutral), Current, Power, Power factor, THD per phase, Frequency, Three phase average voltage and current
Average Values	Voltage (phase-phase, phase-neutral), Voltage min. / max. for phase-phase-phase-neutral, Current, Current min. / max.
Energy Measurement	
Active Energy	Import / Export (high / low tariff)
Reactive Energy	Positive / Negative (high / low tariff)
Apparent Energy	High / low tariff
Energy demand per measuring period	Three-phase average rating for active and reactive power
Min. / Max. rating values within the measuring period	
Meter Running Counter	Uptime in hours
Universal Counter	Pulse counting of external devices like water, gas, etc.
Measurement Accuracy	
Voltages	±0.3
Currents	±0.2
Power Factor and Power	±0.5%
Active Energy	Class 0.5S in acc. with IEC 62053-22 / ANSI 12.20 class 0.5
Reactive Energy	Class 2 in acc. with IEC 62053-23
Monitoring Functions	
Set Point Monitoring	V, I, power, VAR, VA, Freq. THD, PF
Simple Logic Functions	Alarm via digital
Phase Unbalance	Voltage and / or × current
Communication	
Ethernet	Via RJ 45 port - 10 Base-T (10 Mbit/sec)
Modbus TCP	Via RJ 45 port - 10 Base-T (10 Mbit/sec)
Inputs and Outputs	
Digital Input (2)	24 V DC - 7 mA
Digital Output (2)	30 V DC max / 10-27 mA
Technical Data	
Two-Quadrant (import) / Four-Quadrant (Import and Export) measuring	4Q
Measurement Types	1 phase, 2 phases or 3 phases

Parameter	Value
Applicable for Network Types	TN, TT, IT
Sampling Rate	64 samples / cycle at 60Hz
Measured Voltage	347 V (1 phase) / 600 V (3 phases) maximum
Current Inputs	Settable on device, 1 or 5 A nominal
Power Supply	100-250 V ac/dc – 8 VA
Display Type	Background-illuminated graphic LCD, Resolution of 128 x 96 pixels, Multilingual
Physical Characteristics	
Dimensions (H x W x D)	154 x 287 x 410 mm (6.1 x 11.3 x 16.1 in)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com