

RF Generator

8095643 (9505-10)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The RF Generator contains two independent generators capable of producing a CW or 1 kHz square wave AM modulated RF signal at 915 MHz and 10.5 GHz. Each generator has a push-button switch for turning RF power on and off, a LED that flashes on and off when RF power is turned on, and an SMA output connector. The oscillator in the 915 MHz generator can be tuned from 800 to 1200 MHz via an external tuning voltage input. All outputs are fully protected against short-circuits and misconnections. The RF Generator is self-powered and has a standard unregulated dc power bus to supply power to other compatible modules through its top panel connector. The unit beeps when RF power is turned on to help avoid interference and to warn students in the laboratory that RF power is emitted.

Specifications

Parameter	Value
Power Requirement	
Current	1 A
Service Installation	Standard single-phase ac outlet
Unregulated DC Output (Power Bus)	+25 V typ. – 1 A max.; -25 V typ. – 1 A max.; +11 V typ. – 1 A max.
1 GHz RF Power Output	
Impedance	50 Ω
Power Level	+5 dBm (typical); 0 dBm (minimum)
Attenuation at reception	Up to -59 dBm (49 dBm software controlled and 10 dBm with included physical attenuator)
10 GHz RF Power Output	
Impedance	50 Ω
Power Level	+12 dBm (typical)
Attenuation at reception	Up to -59 dBm (49 dBm software controlled and 10 dBm with included physical attenuator)
1 GHz Tuning Voltage Input	
Voltage Range	0-10 V
Frequency Range	800-1200 MHz
Protection	
AC Line Input	Circuit breaker
Unregulated DC Power Bus	Circuit breaker
Physical Characteristics	
Dimensions (H x W x D)	112 x 330 x 300 mm (4.4 x 13.0 x 11.8 in)
Net Weight	6.1 kg (13.4 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com