

# Reconfigurable Training Module (RTM) 8094635 (9431-30)

**FESTO**

**LabVolt Series**

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
12/2024

Table of Contents

General Description	3
Specifications	3

## General Description

The Reconfigurable Training Module (RTM) consists mainly of a powerful digital signal processor (DSP), with three slots on the module front panel for installing interface modules. An Ethernet port (RJ-45) connector, located on the back panel, allows connection of the RTM to the host computer. The functionality of the training system is determined by downloading a program into the DSP memory using the host computer that runs the software. Electrical power is supplied to the RTM by the Power Supply, Model 9408, through a multipin cable that connects to the back panel.

## Specifications

Parameter	Value
<b>Interface Card Slots</b>	
Analog/Digital	2
Digital	1
<b>Data Link</b>	
Data Link to Host Computer	10 Mb/s (Ethernet) or 100 Mb/s (Fast Ethernet), TCP/IP Protocol
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	215 x 430 x 280 mm (8.5 x 16.9 x 11.0 in)
Net Weight	9.8 kg (21.6 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**