

# Four-Module Workstation

## 8110852 (8132-00)

**FESTO**

**LabVolt Series**

Datasheet



\* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic  
en  
04/2025

## Table of Contents

<b>General Description</b>	<b>3</b>
<b>Module Installation</b>	<b>3</b>
<b>Safety Padlock Bars</b>	<b>3</b>
<b>Additional Information</b>	<b>3</b>
<b>Manual</b>	<b>3</b>
<b>Table of Contents of the Manual(s)</b>	<b>4</b>
<b>Specifications</b>	<b>4</b>

## General Description

The Four-Module Workstation is a fully assembled workstation that serves the same purpose as the Mobile Workstation, Model 8110, but without any storage cabinet or pull-out work surface. This workstation is intended for use on a bench (not supplied) and is fitted with wooden feet to protect the bench top.

The Four-Module Workstation consists of two rows of two full-height compartments that can accommodate up to four full-size EMS modules or eight half-size EMS modules.

## Module Installation



The EMS modules are guided into position along stainless steel guide rails. Separators between each bay of the workstation ensure perfect alignment of the EMS modules and allow their easy insertion in the workstation. A holding mechanism ensures that each EMS module stays in place once it is installed in a compartment of the workstation. A front-mounted push lever allows all EMS modules on the workstation to be

released for easy removal.

## Safety Padlock Bars



One safety padlock bar on the front of the workstation prevents students from removing EMS modules during laboratory exercises. The bar can be removed and locked to the side of the workstation when the safety lock is not necessary.

## Additional Information

Two holes in the rear panel of the workstation allow connection to a power supply, as well as the connection of 2 kW machines to their interconnection modules. Assembly of the workstation before painting ensures that each EMS module in the workstation is correctly grounded.

## Manual

### Description

Electric Power Technology Training Equipment (User Guide) \_\_\_\_\_

### Manual number

584778 (38486-E0)

## Table of Contents of the Manual(s)

### Electric Power Technology Training Equipment (User Guide) (584778 (38486-E0))

- 1 General Safety Recommendations
- 2 System Power Requirements
- 3 Quick Start Installation Guide
- 4 Equipment Installation
- 5 Modules Handling, Installation, and Removal
- 6 Equipment Maintenance
- A Connection of the Power Supply to the AC Power Network
- B Description, Specifications, and Operation of the EMS Modules

## Specifications

Parameter	Value
<b>Physical Characteristics</b>	
Dimensions (H x W x D)	750 x 620 x 530 mm (29.6 x 24.4 x 20.9 in)
Net Weight	TBE

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

**Festo Didactic SE**

Rechbergstrasse 3  
73770 Denkendorf  
Germany

P. +49(0)711/3467-0  
F. +49(0)711/347-54-88500

**Festo Didactic Inc.**

607 Industrial Way West  
Eatontown, NJ 07724  
United States

P. +1-732-938-2000  
F. +1-732-774-8573

**Festo Didactic Ltée/Ltd**

675 rue du Carbone  
Québec QC G2N 2K7  
Canada

P. +1-418-849-1000  
F. +1-418-849-1666

**[www.labvolt.com](http://www.labvolt.com)**

**[www.festo-didactic.com](http://www.festo-didactic.com)**