

Analog/Digital Signal Combiner 8112776 (9630-10)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description	3
Specifications	3

General Description

The Analog/Digital Signal Combiner is a compact module designed to be installed into one of the slots on the RTM of the Radar Processor/Display. This module converts the clutter and interference generated by the DSP of the RTM to analog format, and adds it to the I- and Q-channel echo signals coming from the Radar Receiver.

The Analog/Digital Signal Combiner has two BNC-connector inputs to receive the I- and Q-channel echo signals. It also has four BNC-connector outputs. Two outputs provide the clutter and interference signals added to the I- and Q-channel echo signals. The other two outputs provide the I- and Q-channel, perturbed echo signals. All these inputs and outputs are protected from misconnections within the system. Test points are available on the module's front panel to observe all these signals using a conventional oscilloscope.

DC power is automatically supplied to the Analog/Digital Signal Combiner when it is installed into the RTM.

Specifications

Parameter	Value
Analog Inputs (2)	
Voltage Range	-10 to +10 V
Impedance	10 k Ω
Analog Outputs 3 and 4	
Voltage Range	-1 to +1 V
Impedance	600 Ω
Analog Outputs 5 and 6	
Voltage Range	-11 to +11 V
Impedance	600 Ω
Tests Points	
Test Points	6
Physical Characteristics	
Dimensions (H x W x D)	114 x 110 x 209 mm (4.5 x 4.3 x 8.2 in)
Net Weight	0.6 kg (1.4 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com