


Radar Target Tracking Interface

8112778 (9633-10)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Table of Contents

General Description _____	3
Specifications _____	3

General Description

The Radar Target Tracking Interface is a compact module designed to be installed into one of the slots on the RTM of the Radar Processor/Display. The module provides the lobe switching control signal and the RF circuitry (bias tee and DC blocking capacitor) required to perform lobe switching with the Dual Feed Parabolic Antenna. To allow manual or automatic control of the radar antenna rotation, the Radar Target Tracking Interface is also used to intercept the rotation command signal produced by the antenna controller before it reaches the antenna motor driver.

The Radar Target Tracking Interface is provided with four SMA connectors that provide access to the lobe switching RF circuitry. It also has two BNC-connector inputs (lobe switch control input and antenna rotation command input) and two BNC-connector outputs (lobe switch control output and antenna rotation command output). All these inputs and outputs are protected from misconnections within the system. Test points are available on the module's front panel to observe the signals on the BNC-connector inputs and outputs using a conventional oscilloscope.

DC power is automatically supplied to the Radar Target Tracking Interface when it is installed into the RTM.

* **WARNING:** This equipment is subject to export control. Please contact your sales representative to know if this product can be imported in your region.

Specifications

Parameter	Value
RF Inputs and Outputs	
Impedance	50 Ω
Frequency Range	8 to 10 GHz
Lobe Switch Control Input	
Voltage Range	-5 to +5 V
Impedance	1.5 k Ω
Lobe Switch Control Output	
Voltage Range	-5 to +5 V
Impedance	1.0 k Ω
Antenna Rotation Command Input	
Voltage Range	-10 to +10 V
Impedance	10 k Ω
Antenna Rotation Command Output	
Voltage Range	-10 to +10 V
Impedance	600 Ω
Test Points	4
Physical Characteristics	
Dimensions (H x W x D)	114 x 110 x 209 mm (4.5 x 4.3 x 8.2 in)
Net Weight	0.7 kg (1.6 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com