

Radar Phase-Coded Pulse Compression Training System (add-on to the Radar Processor/Display) 8121494 (8097-C0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
12/2024

Table of Contents

General Description	3
Features & Benefits	3
List of Equipment	3
List of Manuals	3
Table of Contents of the Manual(s)	3
Equipment Description	4

General Description

Radar Pulse Compression is a signal processing technique used to increase the range resolution and signal-to-noise ratio of any pulse radar. The design of a radar is usually a question of compromise. In many cases, a trade-off must be made between desirable characteristics. For only a modest increase in cost and complexity, pulse compression improves the range resolution without sacrificing the signal-to-noise ratio. This is why all modern radars use pulse compression.

The Phase-Coded Pulse Compression System is an add-on to the Basic Radar and Radar Processor/Display Training Systems.

* **WARNING:** This equipment is subject to export control. Please contact your sales representative to know if this product can be imported in your region.

The system includes the Phase-Coded Pulse Compression Processor that encodes the radar pulses before transmission and compresses the received pulses. It also includes the Pulse Compression Parabolic Dish Antenna, which is designed to prevent internal reflections from interfering with the radar signal, and two attenuators (4 dB and 10 dB) used to facilitate measurements. The LVRTS software with the Phase-Coded Pulse Compression application is also included. (Note that the LVRTS software is also included with the Radar Processor / Display add-on and can be downloaded from Festo Didactic's website.)

Features & Benefits

- FPGA-based signal processing.
- Seamless integration with the Series Radar Training System.
- User-configurable Pulse Compression Processors for wide topic coverage.
- Multiple test-points for complete learning experience.
- Turnkey solution, including high quality student and instructor manuals.

List of Equipment

Qty	Description	Model number
1	Phase-Coded Pulse Compression (Student Manual) _____	593926 (52919-00)
1	Phase-Coded Pulse Compression (Instructor Guide) _____	593927 (52919-10)
1	Pulse Compression Radar Antenna _____	592570 (9604-B0)
1	Phase-Coded Pulse Compression Processor _____	592571 (9615-00)
1	Accessories Pulse Compression _____	8092757 (9690-G0)

List of Manuals

Description	Manual number
Phase-Coded Pulse Compression (Workbook) _____	593926 (52919-00)
Phase-Coded Pulse Compression (Workbook (Instructor)) _____	593927 (52919-10)
Radar Training System (User Guide) _____	8112390

Table of Contents of the Manual(s)

Phase-Coded Pulse Compression (Workbook) (593926 (52919-00))

- 1-1 Introduction to Phase-Coded Pulse Compression
- 1-2 Basic Concepts and Techniques
- 1-3 Pulse Compression Ratio and SNR Improvement
- 1-4 Phase-Code Compression Processing

- 2-1 Near-Perfect, Pseudo Random, Combined Barker, and Polyphase Codes
- 2-2 Golay Codes and Optimum Mismatched Filters

Equipment Description

Pulse Compression Radar Antenna 592570 (9604-B0)



The Radar Pulse Compression Antenna mounts on the rotating antenna pedestal and is fully compatible with the miniature plug-in RF quick connector. It uses an offset-feed design to reduce masking effects. It also comprises a low-loss cable for adding delay in pulse-compression exercises.

* WARNING: This equipment is subject to export control. Please contact your sales representative to know if this product can be imported in your region.

Specifications :

Dimensions 114 X 110 X 209 mm (4.5 X 4.3 X 8.2 in)

Net Weight 0.6 kg (1.4 lb)

Specifications

Parameter	Value
Type	Offset Feed
Feed Type	Single Horn
Beamwidth (at -3 dB)	6°
Gain	21 dB (typical)
Impedance	50 Ω
Polarization	Linear, vertical
Physical Characteristics	
Dimensions (H x W x D)	425 x 375 x 515 mm (16.8 x 14.8 x 20.3 in)
Net Weight	2.56 kg (5.63 lb)

Phase-Coded Pulse Compression Processor 592571 (9615-00)



The Phase-Coded Pulse Compression Processor allows to experiment pulse compression with the radar training system. It is divided into three sections: Dual-Channel Sampler, Pulse Compressor and Pulse Generator.

The Dual-Channel Sampler samples the I- and Q-Channel baseband signals from the receiver and stretch these signals in time in order to facilitate observation and measurement. It also allows to set the origin (radar display "window") and select the range span. A time base output is available to trig an oscilloscope when displaying the A-Scope.

The Pulse Compressor compresses the pulses by correlating the digital data with the selected code using one or two compressor stages. It allows to select the sample rate of the A/D converter, select the filter mode (matched or optimum mismatched). Test

points are also available to monitor the different signals using an oscilloscope.

The PRF and Sync. signals need to be inputted into the module. Note that only the 288 Hz PRF mode is supported.

The Pulse Generator allows to select the pulse compression code used to encode the baseband pulse.

A switch at the back of the module allows to inject noise into the system to experiment real-life conditions.

* WARNING: This equipment is subject to export control. Please contact your sales representative to know if this product can be imported in your region.

Additional Equipment Required to Perform the Exercises (Purchased separately)

Qty	Description	Model number
1	IEC Power Cable, straight - CEE 7/VII (Type F) _____	789182 (93992-05) ¹
1	IEC Power Cable, straight - NEMA (Type B) _____	789405 (95451-00) ²
1	IEC Power Cable, straight - AS 3112 (Type I) _____	789406 (95451-0A) ³

Specifications

Parameter	Value
Pulse Inputs	
Level	-1V to +1V
Impedance	50 Ω
Connector Type	SMA
A-Scope Time Base Output	
Level	-1V to +1V
Connector Type	BNC
Ranges	Selectable, 1.8m, 3.6m, 7.2m or 12.6m (5.9 ft, 11.8 ft, 23.6 ft or 41.3 ft)
Pulse Generator	

¹ The power cord line is not included with stand-alone Phase-Coded Pulse Compression Processor. Please add the right power cord line for the region. Note that when ordering a system, all power cord lines are included.

² The power cord line is not included with stand-alone Phase-Coded Pulse Compression Processor. Please add the right power cord line for the region. Note that when ordering a system, all power cord lines are included.

³ The power cord line is not included with stand-alone Phase-Coded Pulse Compression Processor. Please add the right power cord line for the region. Note that when ordering a system, all power cord lines are included.

Parameter	Value
Output Impedance	50 Ω
Connector Type	SMA
Pulse Generator / Code and Length	
Barker	4*, 5*, 7*, 13*, 5X7 ns (* normalized or non-normalized)
PRBS	15, 31 ns
Near Perfect	15, 31 ns
Golay	8 ns
Other	Rectangular: 1, 5 ns, Golay: 32 ns
Trigger Inputs	
Connector Type	BNC
Voltage Level	TTL
Pulse Compressor	
Sample Rate	1, 3 samples / ns
Filters	Optimum Mismatch, Matched
Outputs	-1V to +1V
Test Point Monitors	
Outputs	2
Test Points	6
Connector Type	BNC
Level	-1V to +1V
Power Requirements	
From DC Source	15V (60 VA max.)
External Power Adapter	100-240 V AC, 50-60 Hz, 2A
Service Installation	Standard single-phase outlet
Physical Characteristics	
Dimensions (H x W x D)	305 x 330 x 305 mm (12 x 13 x 12 in.)
Net Weight	6.7 kg (14.7 lb)

Accessories Pulse Compression 8092757 (9690-G0)



Accessories for the Phase-Coded Radar Pulse Compression. Includes two attenuators (4dB and 10 dB), longer limiter cables, and a SMA adaptor.

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com