


Stepper Motor 8150979 (8244-10)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
11/2024

Table of Contents

General Description _____ 3

Specifications _____ 3

General Description

The Stepper Motor, Model 8244-1, is an optional Lab-Volt Electromechanical System (EMS) model designed for the study of stepper motor control. This machine uses industrial-grade components and is mounted in a standard-size EMS module. It consists of an 8-lead stepper motor that can be connected either in series or in parallel, depending on the user configuration. It also has high torque capacity and is specifically designed to work in combination with the Microstepping Drive, Model 9018-1.

The module is constructed of heavy gauge steel and is equipped with a metal faceplate including a plastic see-through window. The faceplate can be lowered for access to the machinery and, when closed, is secured by two quick-lock fasteners. All motor leads are terminated on the faceplate by 4-mm safety jacks and are identified by schematic symbols. A geared pulley has been fitted to mechanically couple the motor with another EMS machine through the use of a non-slip timing belt (Model 8942). This flexible belt has molded teeth that mesh with the geared pulley. Tension for the timing belt is provided by the idler tensioning ball bearings mounted on the machine.

Specifications

Parameter	Value
Leads	
	8
Step Angle	
	1.8 degrees
Rotor Inertia	
	0.00449 kg-cm-s ² (0.0623 oz-in-s ²)
Holding Torque	
Unipolar	9.2 N-m (1302 oz-in)
Bipolar	12.0 N-m (1699 oz-in)
Nominal Torque	
	1.4 N-m (198 oz-in)
Bipolar Series Configuration	
Current	4.5 A per phase
Resistance	1.1 Ω per phase
Inductance	12 mH per phase
Bipolar Parallel Configuration	
Current	8.9 A per phase
Resistance	0.26 Ω per phase
Inductance	3 mH per phase
Unipolar Configuration	
Current	6.3 A per phase
Resistance	0.55 Ω per phase
Inductance	3 mH per phase
Physical Characteristics	
Dimensions (H x W x D)	203 x 230 x 187 mm (8 x 9 x 7.4 in)
Net Weight	TBE

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2024. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com