

Hydrogen Fuel Cell 579593 (8803-00)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
09/2023

Table of Contents

General Description	3
Specifications	3

General Description

The Hydrogen Fuel Cell module is a fuel cell stack comprising a fuel cell controller, a hydrogen flow meter, a dc-to-dc converter (required to obtain a regulated dc output from the fuel cell stack), an air supply, and seven LED displays for visualizing all essential system parameters (e.g., current, voltage, temperature, fuel, air supply).

A USB port on the front panel enables use of the included data acquisition software to perform further analysis on the fuel cell stack. This software provides support for the experiments (visualization, data logging, fully automated experiments) in the manual.

Specifications

Parameter	Value
Rated Output	40 W
Maximum Output	50 W
No-Load Voltage	9 V
Current at Rated Output	8 A
Hydrogen Consumption at Rated Output	580 sml/min
Hydrogen Purity for Operation	A minimum of 4.0 (99.99%)
Permissible Hydrogen Pressure	0.4 – 0.8 bar
Permissible Ambient Temperature during Operation	5–35°C (41-95°F)
Communication Port	USB
Pressure Regulator	
Description	Two-stage, hydrogen
Inlet Pressure	Max. 19 bar
Outlet Pressure	0.6 ± 0.1 bar
Accessories	
	Leak detection kit
	Safety connection leads
	Software
Physical Characteristics	
Dimensions (H x W x D)	307 x 579 x 533 mm (12.1 x 22.8 x 21 in)
Net Weight	TBE

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2023. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com