


All-in-One Touch Screen Computer (including Monitor Stand with Articulating Arm) 8108708 (8990-A0)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
05/2025

Table of Contents

General Description	3
Specifications	3

General Description

The All-in-One Touch Screen Computer is a complete computer with a touch screen interface that can be mounted on the side of a standard EMS workstation to connect to workstation instruments such as the Data Acquisition and Control Interface and the Four-Quadrant Dynamometer/Power Supply. It comes with a monitor stand with articulating arm as well as a wireless keyboard and a wireless mouse.

Specifications

Parameter	Value
Scope of delivery	
Includes	All-In-One Touch-Screen Computer, Wireless Keyboard, Wireless Mouse and Monitor Stand with Articulating Arm
Computer	
Operating System	Microsoft Windows 10 Pro
Power	120 W
Display Size	546 mm diagonal (21.5 in)
Processor Family	Intel Core i5
Physical Characteristics	
Dimensions H x W x D (Rack)	280 x 442 x 500 mm fully deployed (11.0 x 17.4 x 19.7 in)
Dimensions H x W x D (Computer)	209 x 489 x 364 mm (8.2 x 19.3 x 14.3 in)
Dimensions H x W x D (Keyboard)	33 x 213 x 453 mm (1.3 x 8.4 x 17.8 in)
Dimensions H x W x D (Mouse)	36 x 68 x 111 mm (1.4 x 2.7 x 4.4 in)
Weight (Complete)	14.8 kg (32.5 lb)

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com