

Virtual Instrument Package

8098535 (1250-20)

FESTO

LabVolt Series

Datasheet



* The product images shown in this document are for illustration purposes; actual products may vary. Please refer to the Specifications section of each product/item for all details. Festo Didactic reserves the right to change product images and specifications at any time without notice.

Festo Didactic
en
05/2025

Table of Contents

General Description	3
Specifications	3

General Description

The Virtual Instrument Package replaces conventional desktop test equipment with a powerful, space-saving, virtual instrumentation package that gives students state-of-the-art tools to measure, analyze, observe, and display the results of electronic circuit tests.

Fully integrated with the FACET® Electronics Training program, the Virtual Instrument Package enables students to conduct all experiments of the FACET® curriculum. The complete Virtual Instrument Package consists of an interface unit for data acquisition connections, and a Windows-based software.

The interface is connected to the computer via a USB connection. The software displays the various instruments in separate windows and includes the following virtual instruments and signal source: a dual-channel oscilloscope, a multimeter, a spectrum analyzer, and a waveform generator.

Complete software suite

The complete Virtual Instrument Package consists of an interface unit for data acquisition connections, and a Windows-based software. The interface is connected to the computer via a USB connection.

This package operates under any one of the following Microsoft Windows operating systems: Windows 7, Windows 8, and Windows 10. It is also possible to interface the unit with MATLAB® and LabVIEW® software for advanced control and analysis.

The interface unit

The Virtual Instrument unit is a lightweight, compact interface module powered from a standard AC power wall outlet.

On the front panel of the Virtual Instrument unit, two BNC connectors and a pair of safety banana sockets provide access to the various virtual instruments. A third BNC connector provides the signal generator output. A BNC connector on the back panel of the Virtual Instrument unit is the access to the external trigger input of the virtual oscilloscope.

The Virtual Instrument unit samples the signals applied to its various inputs to provide raw signal data that is used by the virtual instrument software to measure, filter, and display the input signals. The high sampling rate of 1 GS/s provides the Virtual Instrument unit a 250 MHz bandwidth that is amply sufficient for the observation and analysis of the various signals in the FACET® Electronics Training program.

The Virtual Instrument unit also generates signal samples (data) that are converted to analog format to produce the output signal. Data exchange between the Virtual Instrument unit and the host computer that runs the virtual instrument software is through a USB link (USB 1.1 and 2.0 compatible).

Specifications

Parameter	Value
Oscilloscope / Channels	
Nb channel	2ch
Type	BNC
Sampling rate	500 MS/s max
Range	±200mV to ±80V
Resolution	8, 12, 14, 16 bits, user selectable
Impedance	1 MΩ, 25pF
Oscilloscope / Trigger	
Source	Ch1, Ch2, External
Mode	Rising, Falling, inside/outside window
Level	0 to 100 % of full scale
DMM / Voltage mode	
Range	±200mV to ±80V

Parameter	Value
Accuracy	2% of full scale
Impedance	1 M Ω , 30pF
Protection	200 V
DMM / Current mode	
Range	20mA to 400mA
Accuracy	2% of full scale
Protection	electronic, self restoring fuse, 500mA
DMM / Resistance mode	
Range	100 Ω to 2M Ω
Accuracy	3% of full scale
Signal generator	
Output channel	1 analog, BNC
Resolution	12 bits
Signal type	Sine, square, triangle, arbitrary
Frequency range	0.1 to 20 MHz
Amplitude range	0.12, 1.2, 12 V
Accuracy	0.4 % of full range
Impedance	50 Ω

Reflecting the commitment of Festo Didactic to high quality standards in product, design, development, production, installation, and service, our manufacturing and distribution facility has received the ISO 9001 certification.

Festo Didactic reserves the right to make product improvements at any time and without notice and is not responsible for typographical errors. Festo Didactic recognizes all product names used herein as trademarks or registered trademarks of their respective holders. © Festo Didactic Inc. 2025. All rights reserved.

Festo Didactic SE

Rechbergstrasse 3
73770 Denkendorf
Germany

P. +49(0)711/3467-0
F. +49(0)711/347-54-88500

Festo Didactic Inc.

607 Industrial Way West
Eatontown, NJ 07724
United States

P. +1-732-938-2000
F. +1-732-774-8573

Festo Didactic Ltée/Ltd

675 rue du Carbone
Québec QC G2N 2K7
Canada

P. +1-418-849-1000
F. +1-418-849-1666

www.labvolt.com

www.festo-didactic.com